

TECHNICAL LETTER—SHELF LIFE

Protecto Wrap Self-Adhered Membranes

The shelf life of Protecto Wrap self-adhered membranes is highly dependent on storage conditions. Protecto Wrap self-adhered membrane products should be stored in their original, unopened containers at ambient temperatures between 40°F and 90°F (5°C and 32°C). Storage area should remain dry and out of direct sunlight. Do not remove materials from original containers until ready for use.

Protecto Wrap self-adhered membranes have optimum initial adhesion to substrates when used within one year from the date of manufacture.

Protecto Wrap Company provides the information here based on knowledge and data considered to be true and accurate at the time of publication, and is offered for the user's consideration, verification and investigation. Protecto Wrap Company does not warrant the results to be obtained or the appropriateness of the offering for the user's particular project. It is the sole responsibility of the user to read and understand all statements, recommendations or suggestions regarding conditions of sale. No statement, suggestion or recommendation herein is intended for any use that could infringe on any copyright or patent. These products may be covered by patents or patents pending. Copyright 2008. Protecto Wrap Company

PROTECTO WRAP COMPANY

1955 South Cherokee Street Denver, CO 80223 1-800-759-9727 (303) 777-3001 Fax (303)777-9273 www.protectowrap.com

June 2009